


TITLE: OSL223-RC80A0-UDA2L0-3.0

MARK	AMEND	SIGNATURE
⚠	ADDITIONAL FAN DIRECTION INSTRUCTIONS	Zhou Bolin
⚠	ADDITIONAL INSTALLATION INSTRUCTIONS	Zhou Bolin




"B": M4 Threads, X4 Max Screw Depth=6mm

"C": M4 Threads, X10 Max Screw Depth=10mm


FAN1-6(FAN #4 #6 ARE INTAKE,AND OTHER FANS ARE EXHAUSTS)

DO NOT SCALE DRAWING



GENERAL Touch		General Touch Co.,Ltd.									
SPECIFICATION		OVERALL DIMENSIONS	536x332.7x77.4		ANTI-GLARE		Y	☒	N	☐	DESIGNER: Zhou Bolin
UNIT	DATE	VIEW AREA	475.6x267.1								
MM	2025/12/31	GLASS THICKNESS	6.0 MM								
PROJECTION:		SILK SCREEN COLOR	BLACK								CHECKED BY: Han Jin
		MOUNTING	VESA		☒	BRACKET		☒			
SHEET 1 of 3		NOTES									
VER: 1.1	SCALE: 1:1	TOUCH TECHNOLOGY	P-CAP		☒	SAW				APPROVED BY: Zhou Bolin	
TOLERANCE: ±1.0MM			NON-TOUCH			RESISTIVE					

TITLE: OSL223-RC80A0-UDA2L0-3.0


MARK	AMEND	SIGNATURE
⚠	ADDITIONAL FAN DIRECTION INSTRUCTIONS	Zhou Bolin
⚠	ADDITIONAL INSTALLATION INSTRUCTIONS	Zhou Bolin



RECOMMENDED OPENING SIZE OF CABINET DOOR PANEL




DO NOT SCALE DRAWING


GENERAL Touch		General Touch Co.,Ltd.					
SPECIFICATION		OVERALL DIMENSIONS	536x332.7x77.4		ANTI-GLARE	Y ☒ N ☐	
UNIT	DATE	VIEW AREA	475.6x267.1				DESIGNER:
MM	2025/12/31	GLASS THICKNESS	6.0 MM				Zhou Bolin
PROJECTION:		SILK SCREEN COLOR	BLACK				CHECKED BY:
		MOUNTING	VESA ☒ BRACKET ☒				Han Jin
SHEET 2 of 3		NOTES					APPROVED BY:
VER: 1.1	SCALE: 1:1	TOUCH TECHNOLOGY	P-CAP	☒	SAW		
TOLERANCE: ±1.0MM			NON-TOUCH		RESISTIVE		Zhou Bolin

TITLE: OSL223-RC80A0-UDA2L0-3.0

MARK	AMEND	SIGNATURE
⚠	ADDITIONAL FAN DIRECTION INSTRUCTIONS	Zhou Bolin
⚠	ADDITIONAL INSTALLATION INSTRUCTIONS	Zhou Bolin



STEP 1




STEP 2

STEP 3

INSTALLATION INSTRUCTIONS:

- 1.THIS INSTALLATION METHOD HAS A STEP ON THE SURFACE AFTER INSTALLATION;
- 2.STICK THE WATERPROOF GASKET ON THE CABINET PANEL OR THE GLASS OF THE MONITOR;
- 3.LOCK THE INSTALLATION BRACKET ONTO THE SIDE OF THE MONITOR;
- 4.INSTALL THE MONITOR FROM THE BACK OF THE CABINET PANEL SO THAT THE BOLTS ON THE CABINET PANEL PASS THROUGH THE THROUGH HOLES IN THE BRACKET;
- 5.SQUEEZE SILICONE ADHESIVE INTO THE GAP BETWEEN THE CABINET PANEL AND THE GLASS FROM THE FRONT OF THE CABINET PANEL;

DO NOT SCALE DRAWING

GENERAL Touch		General Touch Co.,Ltd.										
SPECIFICATION		OVERALL DIMENSIONS		536x332.7x77.4		ANTI-GLARE		Y	☒	N	☐	
UNIT	DATE	VIEW AREA		475.6x267.1								DESIGNER:
MM	2025/12/31	GLASS THICKNESS		6.0 MM								Zhou Bolin
PROJECTION:		SILK SCREEN COLOR		BLACK								CHECKED BY:
		MOUNTING		VESA		☒	BRACKET		☒			Han Jin
SHEET 3 of 3		NOTES										
VER: 1.1		SCALE: 1:1		TOUCH TECHNOLOGY		P-CAP		☒	SAW			APPROVED BY:
TOLERANCE: ±1.0MM		NON-TOUCH					RESISTIVE			Zhou Bolin		